


Application Note:

New Wavelength Filtering
Technology for Light Microscopy

[View Details](#)




FWS Auto & Mighty Light

Combination of FWS Auto with
Mighty Light to create a tunable
light source

[FWS Auto](#)

[Mighty Light](#)



Key Product Advantages :

- Fast software controlled wavelength tuning [FWS Auto]
- Software bandwidth adjustment (FWHM 2 – 16 nm) [FWS Auto]
- Low noise ($\pm 0.5\%$) output [Mighty Light]
- Color temperature ~ 2900 K [Mighty Light]

[See All Products](#)

[See All Monthly Newsletters](#)

Wavelength Selector

A truly revolutionary tool for spectroscopy and
spectral imaging.

[View Details](#)



Light Sources

Spectrolight offers a growing selection of
unique light sources and related accessories


[View Details](#)



Optical Components

Spectrolight provides a growing range of
optomechanical components

[View Details](#)



Systems

Spectrolight provides a growing range of
innovative systems and related accessories

[View Details](#)



For Sales and Marketing Inquiries

sales@spectrolightinc.com
949-800-7780

For Applications and Technical
Inquiries

[Jun Hee Kang, Ph. D.](#)
Application Scientist

Email: jkgang@spectrolightinc.com
Mobile: 949-800-5117